

150 series

# CompX eLock for Cabinets

Revolutionizing Electronic Access Control



**CompX eLock® meets Joint Commission requirements!**

### options:

- ◆ Door switch provides instant notification of unauthorized entry or door ajar alerts
- ◆ Using latch splitter, eLock is capable of operating two latches or doors

Network units also available.  
Visit [compixelock.com](http://compixelock.com) for all eLock solutions.

## 150 series eLock®

**Keyless, non-network, electronic access control solution for cabinetry.**

The CompX eLock® for cabinetry can be used in various applications; drug and supply cabinets, key control boxes, medical & personnel records.

### all versions feature:

- ◆ Audit trail of last 1,500 access attempts with date, time and user name
- ◆ 250 user/supervisor codes
- ◆ Six modes of access: Keypad, Proximity card\* HID, iCLASS, iCLASS SE, MiFARE and DESFire smart cards \*Use existing identification cards
- ◆ Motor driven latching mechanism
- ◆ 6-AA battery pack; premium brand Alkaline batteries recommended (not included)
- ◆ Low battery indicator
- ◆ Jump start battery override available through mini USB communications port allows the user, with a valid credential, to access the CompX eLock® when the batteries are exhausted
- ◆ Tamper resistant locking bolt with audible alarm
- ◆ Mini USB communications port for audit trail download with **optional** LockView 5 software
- ◆ Compatible with 12-volt electric door strikes to control access on interior doors

**CompX**  
SECURITY PRODUCTS

Reorder #: F2644-035

Copyright 2021 © CompX Security Products / 847.752.2500 / [comp.x.com](http://comp.x.com) / 715 Center St., Grayslake, IL 60030  
Any companies and/or products referred to herein are marks or registered trademarks of their respective companies, owners and/or mark holders.

For more information, call **847.752.2500**

# LockView SOFTWARE


## LockView® 5 software features:

LockView® makes it easy to monitor audit trails for the last 1,500 access attempts, manage users and eLocks, and assign time-based restrictions and dual credential access. Downloading and uploading information is simple. Attach mini USB to communications port on eLock and standard USB to laptop.

- ◆ Provides a comprehensive audit trail of the last 1,500 access attempts; including date, time and user name
- ◆ Complies with Joint Commission standards and is 21 CFR Part 11 compliant
- ◆ When connected, LockView sends updates to the eLock. Updates can include:
  - User changes (Add / Delete / Modify Credentials)
  - eLock Changes (Add / Delete / Modify eLocks)
  - Access Rights changes
- ◆ LockView software sold separately


### Minimum System Requirements

Windows 7, 8, 8.1, 10; 4GB RAM (8GB recommended), Processor 2.0 GHz or higher, 4GB Hard drive space. Other configurations are acceptable; please consult factory for detailed information.




150 series **cabinet** eLock has three components:


### Controller



### Motorized gear-driven latch



### Battery compartment



**CompX**  
SECURITY PRODUCTS



Reorder #: F2644-035

Copyright 2021 © CompX Security Products / 847.752.2500 / compx.com / 715 Center St., Grayslake, IL 60030  
Any companies and/or products referred to herein are marks or registered trademarks of their respective companies, owners and/or mark holders.

For more information, call **847.752.2500**